



DATA SHEET

POLISHING PASTE POLISTRAT

POLISTRAT has been developed specially for the polishing of the contact surfaces of moulds.
It is used for fast cleaning and restoration of the original shine.
For new moulds, and after polishing with abrasive paper, **POLISTRAT** provides excellent results.
Where appropriate, it can also be used to achieve a gloss on the finished parts

PHYSICAL CHARACTERISTICS

Appearance: White-coloured oily paste or blue
Density: > 1
No flammable.
Odourless and non-toxic.
Contains mild abrasives.

APPLICATION

POLISTRAT was designed to be used with a polishing machine (sheepskin), but can be applied by hand as a last resort.
Deposit a small quantity of **POLISTRAT** onto the surface to be treated, and shine up.
Treat a small area at a time.
Treat this operation until the required gloss is obtained.
The shine can be improved still further by use of **LUSTRAT**, our liquid polishing product.

PACKING AND STORAGE

Packaging : 500 g and 5 kg
Storage: Away from frost and at a temperature of less than 50°C.
Run-out date: 24 months

PRECAUTIONS FOR USE

Wash hands after use. Lightly irritating to eyes and skin. In case of prolonged contact with the skin, rinse with plenty of water. Keep out of reach of children.

HEALTH AND SAFETY

See data sheet

This information corresponds to the actual state of our knowledge and has the sole object of informing you about our products and possible applications. It is objectively given but does not imply any guarantee by us.
Our company may modify all these details at any time